

Hangzhou Color Powder Coating Equipment Co.,Ltd



COLO
www.colourspray.com ↗

You Tube
<https://www.youtube.com/user/colopowdercoatinggun>

WeChat
himytom

f
<https://www.facebook.com/hicolo>

Why choose plastic powder coating booth ?



The transparent plastic powder spray booth compared with the metal housing spray booth its obvious technical advantages:

- ◆ plastic powder booth inner wall of the high-voltage electrostatic field, due to the charge with the same polarity with powder particles to form the inner wall of the rebound effect of the powder particles powder booth polarity repulsion, so that more of the powder to the workpiece aggregation, thereby effectively improving the efficiency of spraying.
- ◆ Let the powder booth inner wall of the amount of powder adsorbed to the least, the spray system to reduce the amount of powder overspray, the extraction rate increase will help save powder.
- ◆ transparent powder spray in favor of operating room personnel to observe and monitor working conditions.
- ◆ blown with compressed air gun can be easily attached to the inner wall of dusting powder, powder room conducive to quick cleaning.
- ◆ COLO Series powder coating system, dusting powders, recovery and recycling techniques to a new level.
- ◆ with transparent plastic for polymer let the powder booth has the best effect.

