

IND890 Applications



Stand-Alone Solution for Advanced Statistical Quality Control



ICPAS

Statistical Quality Control With a Flexible, Touch-Screen Terminal

- Full control of filling process
- Advanced quality management system
- Save costs by reducing overfilling
- Easy product management
- Touch-screen data entry
- USB stick for data transfer
- Statistic reports for documentation

IND890SQC weighing solutions from METTLER TOLEDO is integrated with the SQC-890 application to optimize the production process. It is cost-effective, as it eliminates expensive product giveaway from overfilling. With SQC-890, production quality increases and the filling process can be fully controlled.

IP69K for difficult environments

The IND890's robust stainless-steel housing allows it to survive in the harshest industrial environments. All components are specified to ensure long service life.

Cost-effective accuracy

Control systems must be simple to operate, fast, reliable and objective. Statistical Quality Control (SQC) helps in the production to ensure consistently high quality.

Align with legal requirements

The SQC-890 application enables the control of illegal under-fillings, which can be monitored, documented and then eliminated.



10 24 04 1 5 00 m 11 5 04 1 5 00 m 12 5 04 1 5 00 m 13 1 0 0 1 5 00 m 14 5 04 1 5 00 m 15 1 0 0 1 5 0 0 m 16 1 0 0 1 5 0 0 m 16 1 0 0 1 5 0 0 m 16 1 0 0 0 1 5 0 0 m 17 1 0 0 1 1 0 0 0 m 18 10 0 0 m 1 0 0 0 m 19 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 m 1 0 0 0 m 10 1 0 0 0 0 m 1 0 0 0 0 m 10 <t< th=""><th>Article: Musler: Runitel:</th><th colspan="2">Bath Cars aniosinstrum bouto at</th><th>Die Dare:</th><th colspan="2">35771, 5 9966, 81 78, 81 80</th></t<>	Article: Musler: Runitel:	Bath Cars aniosinstrum bouto at		Die Dare:	35771, 5 9966, 81 78, 81 80	
Name: 15:01:07 15:01 Des: 01:01:01 10:01:01 Name: 10:01:01 10:01:01 Note with the second secon	11- 121	1.00 1	\$100 H 1100 H 1100 H			
Inst. Prof. mer. 105.32 + 35.40.81 Technics visibilities 9 + 40.9 9 + 40.9 Prof. mer. 10.53 + 4.40.98.1 9 + 9.40.9 1.40.9 Rescinant 10.53 + 4.40.98.1 9 + 9.40.9 1.40.9 Rescinant 10.54 + 4.40.98.1 9 + 9.40.9 1.40.9 Rescinant 10.54 + 4.40.98.1 9 + 9.1 1.40.9 Rescinant 10.84.9 1.74.2 K 9 + 9.1 1.40.9 Rescinant 10.84.9 1.74.2 K 9 + 9.1 1.40.9 Rescinant 1.80.9 2.40.9 1.40.9 1.40.9 Rescinant 1.40.9	Statt manth	the sample.	NO 2 10 10 100			
Intro. State Control State Contro State State <td>Bank) 22.78.</td> <td>10.15.14</td> <td></td> <td>End</td> <td>82.16.25 25.47</td> <td></td>	Bank) 22.78.	10.15.14		End	82.16.25 25.47	
dD 4.04 1 4.1 10.10 1 10 dD1 4.04 1 4.1 10.10 1 10 dD1 4.04 1 4.1 10.10 1 10 dD1 1.07 1 4.1 10.10 1 1 d1 1.07 1 10.10 1 1 1 1 d1 1.07 1 10.10 1 <td>Fox. Der. Schoum National</td> <td>3.84 % .89.74 %</td> <td>2.455 m. 44.75 m. 50.11 m.</td> <td>472- 472-</td> <td>1</td> <td>1.01 %</td>	Fox. Der. Schoum National	3.84 % .89.74 %	2.455 m. 44.75 m. 50.11 m.	472- 472-	1	1.01 %
197 B	BEETTON MARK	2.28 % 1.85 % 2.27 % 8.67 % 11.87 %	1		14.00 1 14.00 1 3.00 1 - 1.10 1 1.47 1	
	10					
3 F	Zan					

IND890SQC produces clear text printed out on strip printers, A4 paper or as PDFs.



Benefits

Easy Compliance

A large number of products can be defined in the product catalogue. For each product, one of four different tolerance systems can be selected. These tolerance systems support customers in complying with national and international net content legislations as well as global guidelines, such as British Retail Consortium (BRC), International Featured Standards for Food (IFS) and International Organization of Legal Metrology (OIML R 87).

Also, the operator will directly be notified if a change in the filling process is needed to take immediate action.



Informed Decision-Making

Two statistical reports can be created per product. They are provided to evaluate different production periods. Armed with this valuable information, leaders can make better decisions to better control their processes.

Flexible Data Access

Reports and statistics can be stored on a USB stick for easy data transportation. It can also be stored on a server location and accessed from anywhere within the company network.



Security Assurance

Different user profiles are defined for enhanced security, which regulates each user's responsibilities. The different profiles have allocated functions such as access to different features, language and SQC settings. This ensures operators can access only areas of the system they need.

Simple Connectivity

The system supports connection of peripheral interface devices, such as bar code scanners, USB sticks and tablet feeder LV11.



Technical Data

Touchscreen interface	Standard on all models at 10" size, measured diagonally.		
Environmental protection	IP69K, suitable for harsh industrial environ- ments. Rust-		
	free housing with Ra<0.8µm surface finish.		
Display	Easy to read with intuitive interface and icons.		
	DeltaTrac display for easy weighing-to-target		
Data storage	Compact flash-card storage standard in all models.		
Scale interface	Scale interfaces include analog, IDNet, SICS and SICSpro.		
Connectivity	Ethernet connectivity is standard for integration into		
	industrial networks. In addition, select and install up to		
	six interfaces including scales, USB, and serial (RS-232)		
	for connection to PCs, printers and bar-code scanners.		
HMI display options	Available in panel-mount and harsh enclosure designs.		
	Harsh includes ergonomic and swivel mount for wall or		
	desk mounting.		











For more information

Mettler-Toledo AG

Industrial CH-8606 Greifensee Switzerland Tel +41 44 944 22 11 Fax +41 44 944 30 60

Subject to technical changes ©10/2013 Mettler-Toledo AG Printed in Switzerland 44098577